

UNCONTROLLED DOCUMENT

Ø 12.60
10.90

1.90
1.60

2.80
2.40

4.70 MAX

M6 X 1.0 THREADS

92°
90°

3.30 MAX REF

40.00±0.5

ALL DIMENSIONS ARE IN MILLIMETERS
TOLERANCES UNLESS NOTED

±.13MM ON DIMENSIONS THRU 15.88MM
±.20MM ON DIMENSIONS 15.89MM THRU 25.41MM
±.25MM ON DIMENSIONS 25.42MM THRU 38.10MM
±.38MM ON DIMENSIONS LARGER THAN 38.10MM

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

PROPERTY OF
MICRO PLASTICS INC.

CATALOG DRAWING
OVAL SLOTTED MACHINE SCREW
MICRO P/N 50M060100L040
DWG. # 50M060100L040
FILE SERVER\ENG\WEB

MATERIAL: 6/6 NYLON

DATE

SCALE
2:1

TA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

50M060100L040