


# UNCONTROLLED DOCUMENT

NOTES:

CLAMPING RANGE .311 / .362



.187±.015

.062±.015

## TOLERANCES UNLESS NOTED

±.005 ON DIMENSIONS THRU .625

±.008 ON DIMENSIONS .626 THRU 1.000

±.010 ON DIMENSIONS 1.001 THRU 1.500

±.015 ON DIMENSIONS LARGER THAN 1.500

±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS

PROPERTY OF  
**MICRO PLASTICS INC.**

CATALOG DRAWING  
5/16" DOUBLE GRIP HOSE CLAMP  
MICRO P/N 22DGHC00B  
DWG. # 22DGHC00B  
FILE SERVER\ENG\WEB

**MATERIAL:** NYLON 6/6; MOLD BLACK

DATE

SCALE  
3:1

**TA**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[22DGHC00B](#)