


UNCONTROLLED DOCUMENT

NOTES:
CLAMPING RANGE 1.811 / 1.988



TOLERANCES UNLESS NOTED

- ±.005 ON DIMENSIONS THRU .625
- ±.008 ON DIMENSIONS .626 THRU 1.000
- ±.010 ON DIMENSIONS 1.001 THRU 1.500
- ±.015 ON DIMENSIONS LARGER THAN 1.500
- ±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

PROPERTY OF		
MICRO PLASTICS INC.		
CATALOG DRAWING 1-7/8" DOUBLE GRIP HOSE CLAMP MICRO P/N 22DGHC00U DWG. # 22DGHC00U FILE SERVER\ENG\WEB		
MATERIAL: NYLON 6/6; MOLD BLACK		
DATE	SCALE 1:1	TA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[22DGHC00U](#)