



UNCONTROLLED DOCUMENT

NOTES:  
CLAMPING RANGE 2.756 / 2.969



$.359 \pm .015$

$.093 \pm .015$



TOLERANCES UNLESS NOTED

- $\pm .005$  ON DIMENSIONS THRU  $.625$
- $\pm .008$  ON DIMENSIONS  $.626$  THRU  $1.000$
- $\pm .010$  ON DIMENSIONS  $1.001$  THRU  $1.500$
- $\pm .015$  ON DIMENSIONS LARGER THAN  $1.500$
- $\pm .015$  ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS

PROPERTY OF  
**MICRO PLASTICS INC.**

CATALOG DRAWING  
2-7/8" DOUBLE GRIP HOSE CLAMP  
MICRO P/N 22DGHC070  
DWG. # 22DGHC070  
FILE SERVER\ENG\WEB

MATERIAL: NYLON 6/6; MOLD BLACK

DATE	SCALE 1:1	<b>TA</b>
------	--------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[22DGHC070](#)