


# UNCONTROLLED DOCUMENT

NOTES:  
CLAMPING RANGE .360 / .410



## TOLERANCES UNLESS NOTED

±.005 ON DIMENSIONS THRU .625  
±.008 ON DIMENSIONS .626 THRU 1.000  
±.010 ON DIMENSIONS 1.001 THRU 1.500  
±.015 ON DIMENSIONS LARGER THAN 1.500  
±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS

PROPERTY OF  
**MICRO PLASTICS INC.**

CATALOG DRAWING  
HOSE CLAMP  
MICRO P/N 22HSC0040  
DWG. # 22HSC0040  
FILE SERVER\ENG\WEB

MATERIAL: NYLON 6/6

DATE

SCALE  
2:1

**TA**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[22HSC0040](#) [22HSC0040B](#)