





PART NO.	"L" BODY LENGTH	"A" BODY DIAMETER	"B" STUD LENGTH	"C" NOT THREADED	"D" INSERT DEPTH	THREAD
TN4-12-632	3/4 (19.1)	1/4 (6.4)	1/4 (6.4)	1/16 (1.6)	11/64 (4.4)	#6-32
TN4-16-632	1 (25.4)					
TN4-20-632	1-1/4 (31.8)					
TN4-24-632	1-1/2 (38.1)					
TN4-28-632	1-3/4 (44.5)					
TN4-32-632	2 (50.8)	3/8 (9.5)	1/4 (6.4)	1/16 (1.6)	3/16 (4.8)	#8-32
TN6-16-832	1 (25.4)					
TN6-20-832	1-1/4 (31.8)					
TN6-24-832	1-1/2 (38.1)					
TN6-28-832	1-3/4 (44.5)					
TN6-32-832	2 (50.8)	1/2 (12.7)	9/32 (7.1)	3/32 (2.4)	3/16 (4.8)	#10-24
TN6-36-832	2-1/4 (57.2)					
TN6-40-832	2-1/2 (63.5)					
TN8-14-1024	7/8 (22.3)					
TN8-20-1024	1-1/4 (31.8)					
TN8-24-1024	1-1/2 (38.1)	5/8 (15.9)	7/16 (11.1)	1/8 (3.2)	21/64 (8.3)	1/4-20
TN8-28-1024	1-3/4 (44.5)					
TN8-32-1024	2 (50.8)					
TN8-36-1024	2-1/4 (57.2)					
TN8-40-1024	2-1/2 (63.5)					
TN10-20-1/420	1-1/4 (31.8)	5/8 (15.9)	7/16 (11.1)	1/8 (3.2)	21/64 (8.3)	1/4-20
TN10-24-1/420	1-1/2 (38.1)					
TN10-28-1/420	1-3/4 (44.5)					
TN10-32-1/420	2 (50.8)					
TN10-36-1/420	2-1/4 (57.2)					
TN10-40-1/420	2-1/2 (63.5)					

NOTES:

- MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01),
COLOR: WHITE.
THREADED INSERTS/STUDS: BRASS (RMS-231)

H	SEE CO 200773 FOR CHANGES	SK 04.30.12	TITLE: THREADED NYLON STURDIPOST					DWG IN IN (MM)	
G	SEE ECN 1270 FOR CHANGES	SK 01.10.07							
F	SEE ECN 1261 FOR CHANGES	SK 12.06.06	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=1/64 ANG=1°				PART # SEE TABLE	PRINT TYPE CA	
E	SEE ECN 1214 FOR CHANGES	SK 09.12.06							
D	SEE ECN 1164 FOR CHANGES	SJ 05.09.06	FILE # TN		DWN: P.B.	APP:	FINAL		
C	CHANGED FILE NUMBER	SM 05.10.01	MAT'L: SEE NOTES		DT: 08-02-94	DT:			
B	ADDED NOTE: MAJOR DIA. OF THREAD	JL 11.12.98	RE: RICHCO, INC.		RICHCO INC. PO BOX 804238,CHICAGO,60680 (773) 539-4060				
A	CONVERTED TO ACAD	PB 08.02.94							
REV	DESCRIPTION	ENGR DATE							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[TN10-36-1/420-1](#) [TN4-20-632-1](#) [TN6-32-832-3](#) [TN10-28-1/420-1](#) [TN8-32-1024-3](#) [TN4-32-632-2](#) [TN4-16-632-2](#)
[TN10-20-1/420-1](#) [TN10-20-1/420-2](#) [TN10-20-1/420-3](#) [TN10-24-1/420-1](#) [TN10-24-1/420-2](#) [TN10-24-1/420-3](#) [TN10-28-1/420-2](#) [TN10-28-1/420-3](#) [TN10-32-1/420-1](#) [TN10-32-1/420-2](#) [TN10-32-1/420-3](#) [TN10-36-1/420-2](#) [TN10-36-1/420-3](#)
[TN10-40-1/420-1](#) [TN10-40-1/420-2](#) [TN10-40-1/420-3](#) [TN4-12-632-1](#) [TN4-12-632-2](#) [TN4-12-632-3](#) [TN4-16-632-1](#) [TN4-16-632-3](#) [TN4-20-632-2](#) [TN4-20-632-3](#) [TN4-24-632-1](#) [TN4-24-632-2](#) [TN4-24-632-3](#) [TN4-28-632-1](#) [TN4-28-632-2](#) [TN4-28-632-3](#) [TN4-32-632-1](#) [TN4-32-632-3](#) [TN6-16-832-1](#) [TN6-16-832-2](#) [TN6-16-832-3](#) [TN6-20-832-1](#) [TN6-20-832-2](#) [TN6-20-832-3](#) [TN6-24-832-1](#) [TN6-24-832-2](#) [TN6-24-832-3](#) [TN6-28-832-1](#) [TN6-28-832-2](#) [TN6-28-832-3](#) [TN6-32-832-1](#) [TN6-32-832-2](#) [TN6-36-832-1](#) [TN6-36-832-2](#) [TN6-36-832-3](#) [TN6-40-832-1](#) [TN6-40-832-2](#) [TN6-40-832-3](#)
[TN8-14-1024-1](#) [TN8-14-1024-2](#) [TN8-14-1024-3](#) [TN8-20-1024-1](#) [TN8-20-1024-2](#) [TN8-20-1024-3](#) [TN8-24-1024-1](#) [TN8-24-1024-2](#) [TN8-24-1024-3](#) [TN8-28-1024-1](#) [TN8-28-1024-2](#) [TN8-28-1024-3](#) [TN8-32-1024-1](#) [TN8-32-1024-2](#) [TN8-36-1024-1](#) [TN8-36-1024-2](#) [TN8-36-1024-3](#) [TN8-40-1024-1](#) [TN8-40-1024-2](#) [TN8-40-1024-3](#)