



UNCONTROLLED DOCUMENT



NOTES:
 HOLE SIZE: .875
 MAXIMUM PANEL THICKNESS: .125
 MAXIMUM I.D. : .562
 MATERIAL: HEAT STABILIZED NYLON UL 94V2
 STOCKED IN STANDARD BLACK
 TEMPERATURE INDEX: 105° C
 WHITE AVAILABLE UPON REQUEST



TOLERANCES UNLESS NOTED

- ±.005 ON DIMENSIONS THRU .625
- ±.008 ON DIMENSIONS .626 THRU 1.000
- ±.010 ON DIMENSIONS 1.001 THRU 1.500
- ±.015 ON DIMENSIONS LARGER THAN 1.500
- ±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT
 TO DISCONTINUE ITEMS,
 CHANGE SPECIFICATIONS
 OR DESIGN AT ANY TIME
 WITHOUT NOTICE AND
 WITHOUT INCURRING
 ANY OBLIGATIONS

PROPERTY OF
MICRO PLASTICS INC.

CATALOG DRAWING
 ALL-FIT ADJUSTABLE BUSHING
 MICRO P/N 22AF0875
 DWG. # 22AF0875
 FILE SERVER\ENG\WEB

MATERIAL:		AS NOTED
DATE	SCALE	JDD
	3:1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[22AF0875](#)