


UNLESS OTHERWISE STATED

ALL DIMENSIONS IN mm				DO NOT SCALE
LINEAR TOLERANCE				THIRD ANGLE PROJECTION
SIZE	(0)	(0.0)	(0.00)	
0-10mm	±0.5	±0.15	±0.10	
>10-30	±0.5	±0.20	±0.15	
>30-50	±0.5	±0.30	±0.20	
>50-100	±0.8	±0.50	±0.25	
>100-200	±1.5	±0.80	±0.40	
>200-300	±2.0	±1.20	±0.80	
>300-500	±3.0	±2.00	±1.00	
>500	±5.0	±3.00	±1.50	
				ANGULAR TOLERANCE ±0.5 DEGREES
				UNSPECIFIED RADII 0.25mm
				DRAFT ANGLE 0.5 DEGREES
				DIMENSIONS IN BRACKETS [] ARE IN INCHES FOR REFERENCE ONLY

ORG. SCALE: 2:1 CREATE DATE: 11/12/2018

MATERIAL: PA 66

Part ID: 1456123 Project: P160230-1

TITLE: GROMMET NUT 1.19-4.57 H 2.04

DWG. No. 60SGN01179





SHEET	1 of 1
ISSUE	1

NOTES :

HOLE SIZE : 9.4 / 11.3

THICKNESS RANGE : 1.57/3.05

SCREW SIZE : 1/4



1:1

APPROVED - UNCONTROLLED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[60SGN01179](#)