



PART NUMBER		ADHESIVE TAPE	BUNDLE Ø RANGE REF.	"A"±.015 [±0.4]	"B"±.015 [±0.4]	"C" REF.	"D"	
UL94 V-2 NYLON	UL94 V-0 NYLON							
AKKL-2140-01	AKKL-2140-19	NONE	.215-.258 [5.5-6.5]	.85 [21.6]	.650 [16.5]	.708 [18.0]	.39 [10.0]	
AKKL-2140A-RT	AKKL-2140A-19	1/32" THICK RUBBER TAPE (RMS-136)						
AKKL-3140-01	AKKL-3140-19	NONE	.312-.406 [7.9-10.3]	1.00 [25.4]	.750 [19.1]	.866 [22.2]	.40 [10.2]	
AKKL-3140A-RT	AKKL-3140A-19	1/32" THICK ACRYLIC TAPE (RMS-15)						
AKKL-3140-DHB	-	.04" THICK HIGH BOND ACRYLIC TAPE (RMS-500)						
AKKL-4756-01	AKKL-4756-19	NONE						
AKKL-4756A-RT	AKKL-4756A-19	1/32" THICK ACRYLIC TAPE (RMS-15)	.469-.562 [11.9-14.3]	1.25 [31.8]		1.09 [27.8]	1.25 [31.8]	.50 [12.7]
AKKL-4756-DHB	-	.04" THICK HIGH BOND ACRYLIC TAPE (RMS-500)						
AKKL-5775-01	AKKL-5775-19	NONE	.578-.750 [14.7-19.1]	1.50 [38.1]		1.25 [31.8]	1.75 [44.5]	
AKKL-5775A-RT	AKKL-5775A-19	1/32" THICK ACRYLIC TAPE (RMS-15)						
AKKL-8710-01	AKKL-8710-19	NONE	.875-1.00 [22.2-25.4]	2.00 [50.8]	1.00 [25.4]	1.75 [44.5]		
AKKL-8710A-RT	AKKL-8710A-19	1/32" THICK ACRYLIC TAPE (RMS-15)						
AKKL-10112-01	AKKL-10112-19	NONE	1.00-1.25 [25.4-31.7]	2.5 [63.5]	2.00 [50.8]	2.00 [50.8]		
AKKL-10112A-RT	AKKL-10112A-19	1/16" THICK ACRYLIC TAPE (RMS-15)						



TYPICAL RELEASE
TAB LOCATION. TAB
NOT AVAILABLE WITH
-DHB PARTS

NOTES:

1. MATERIAL: UL94 V-2 NYLON 6/6 (RMS-01) OR UL94V-0 NYLON 6/6 (RMS-19)
2. COLOR: NATURAL.
3. STANDARD ACRYLIC ADHESIVE TAPE (RMS-15), WHITE LINER.
HIGH BOND ACRYLIC TAPE (RMS-500), RED LINER
4. BY SPECIAL ORDER ONLY, RUBBER ADHESIVE TAPE (RMS-102), BLUE LINER,
TO ORDER USE P/N: AKKL-XXXXA1-RT OR AKKL-XXXXA1-19

P	ADDED -3140-DHB & -4756-DHB PARTS, ECN # 1429	DZ	04/05/2017	TITLE: ADJUSTABLE KWIK KLIP						UNITS: INCH [mm]							
O	SEE CO200773 FOR CHANGES	SK	04/30/2012														
N	SEE ECN #952 FOR CHANGES	SK	02/25/2005	CREATED USING SOLIDWORKS		FILE #: AKKL		DWN: SM		APP: -		FINAL					
M	SEE ECN #939 FOR CHANGES	SK	02/10/2005														
L	SEE ECN #847 FOR CHANGES	SM	09/10/2004	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°		SHEET: 1 OF 1		SHEET SIZE: A		DT: 12/02/2003		CHKD: -		PART # SEE TABLE		PRINT TYPE CA	
K	SEE ECN #750 FOR CHANGES	SM	01/27/2004														
J	SEE ECN #733 FOR CHANGES	SM	12/02/2003														
-	SEE ENGINEERING FOR REVISION HISTORY (A-I)	-	-														
REV.	DESCRIPTION	ENGR.	DATE			ESSENTRA		COMPONENTS									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[AKKL-3140-DHB](#) [AKKL-2140A-19](#) [AKKL-4756A-RT](#) [AKKL-4756A-19](#) [AKKL-10112A-19](#) [AKKL-10112A-RT](#) [AKKL-2140A-RT](#) [AKKL-3140A-19](#) [AKKL-3140A-RT](#) [AKKL-5775A-19](#) [AKKL-5775A-RT](#) [AKKL-8710A-19](#) [AKKL-8710A-RT](#) [AKKL-3140-01](#) [AKKL-3140-19](#) [AKKL-4756-01](#) [AKKL-4756-19](#) [AKKL-4756-DHB](#) [AKKL-5775-01](#) [AKKL-5775-19](#) [AKKL-5775-DHB](#) [AKKL-8710-01](#) [AKKL-8710-19](#)