


|                              |     |      |
|------------------------------|-----|------|
| Material: UL94 V-2 Nylon 6/6 |     |      |
| Color: Natural               |     |      |
| Part No.                     | A   |      |
|                              | mm  | in   |
| CBABS205A                    | 3.5 | .138 |
| CBABS210A                    | 4.8 | .189 |
| CBABS215A                    | 6.4 | .252 |
| CBABS220A                    | 8   | .315 |
| CBABS225A                    | 10  | .394 |

TO SNAP LOCK IN A 3 (.118) Ø HOLE, IN A  
1.2 - 1.6 (.047 - .062) PANEL THICKNESS



TOLERANCES  
UNLESS NOTED  
≤ 5 mm ±0.2  
5 - 20 mm ±0.3  
20 - 40 mm ±0.4  
40 - 60 mm ±0.5  
60 - 100 mm ±0.8  
≥ 100 mm ±1.0

|                                           |  |                     |  |
|-------------------------------------------|--|---------------------|--|
| TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT |  | DWG IN<br>MM (IN)   |  |
| FILE# CBABS2XX                            |  | PART #              |  |
| SHEET: 1 OF 1                             |  | DT: 01/08/15        |  |
| RE:                                       |  | SEE TABLE           |  |
| ESSENTRA<br>COMPONENTS                    |  | PRINT<br>TYPE<br>CA |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBABS210A](#) [CBABS215A](#) [CBABS205A](#) [CBABS220A](#) [CBABS225A](#)