


Material: UL94 V-2 Nylon 6/6			
Color: Natural			
Part No.	A		in
	mm		
CBDLS105A	6		.236
CBDLS110A	8		.315
CBDLS115A	10		.394
CBDLS120A	12		.472
CBDLS125A	13		.512
CBDLS130A	14		.551
CBDLS135A	16		.630
CBDLS140A	16.8		.661
CBDLS145A	18		.709
CBDLS150A	20		.787

TO SNAP LOCK IN A 4 (.156) Ø HOLE, IN A
1.6 (.062) PANEL THICKNESS



TO SNAP LOCK IN A 4 (.156) Ø HOLE, IN A
1.6 (.062) PANEL THICKNESS

TOLERANCES
UNLESS NOTED
≤ 5 mm ±0.2
5 - 20 mm ±0.3
20 - 40 mm ±0.4
40 - 60 mm ±0.5
60 - 100 mm ±0.8
≥ 100 mm ±1.0

TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT					DWG IN MM (IN)	PRINT TYPE CA
	FILE: CBDLS1XX		DWN: CLC		PART # SEE TABLE	
	SHEET: 1 OF 1	SHEET SIZE: A	DT: 01/08/15			
	RE:					
						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBDLS105A](#) [CBDLS110A](#) [CBDLS115A](#) [CBDLS120A](#) [CBDLS125A](#) [CBDLS130A](#) [CBDLS135A](#) [CBDLS140A](#)
[CBDLS145A](#) [CBDLS150A](#)