


Material: UL94 V-2 Nylon 6/6

Color: Natural

Part No.	A	
	mm	in
CBDLS505A	3.2	.126
CBDLS510A	5	.197
CBDLS515A	6.4	.252
CBDLS520A	7	.276
CBDLS525A	8	.315
CBDLS530A	9.5	.374
CBDLS535A	11.2	.441
CBDLS540A	12	.472
CBDLS545A	15	.591
CBDLS550A	16	.630
CBDLS555A	17	.669
CBDLS560A	20	.787
CBDLS565A	22	.866
CBDLS570A	25.4	1.000

TO SNAP LOCK IN A 3 (.118) Ø HOLE, IN A
1.2 - 2 (.047 - .078) PANEL THICKNESS



TO SNAP LOCK IN A 3 (.118) Ø HOLE, IN A
1.2 - 2 (.047 - .078) PANEL THICKNESS

TOLERANCES	±0.2
UNLESS NOTED	±0.3
≤ 5 mm	±0.4
5 - 20 mm	±0.5
20 - 40 mm	±0.8
40 - 60 mm	±1.0
60 - 100 mm	
≥ 100 mm	

TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT		  DWG IN MM (IN)	
FILE: CBDLS5XX SHEET: 1 OF 1 RE:	SHEET SIZE: A	DWN: CLC DT: 01/08/15	PART # SEE TABLE
	 ESSENTRA COMPONENTS		PRINT TYPE CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBDLS540A](#) [CBDLS570A](#) [CBDLS555A](#) [CBDLS510A](#) [CBDLS515A](#) [CBDLS525A](#) [CBDLS560A](#) [CBDLS550A](#)
[CBDLS520A](#) [CBDLS530A](#) [CBDLS505A](#) [CBDLS545A](#) [CBDLS535A](#) [CBDLS565A](#)