


Material: UL94 V-2 Nylon 6/6

Color: Natural

Part No.	A	
	mm	in
CBDLS605A	3.2	.126
CBDLS610A	4	.157
CBDLS615A	4.8	.189
CBDLS620A	6.4	.252
CBDLS625A	7	.276
CBDLS630A	8	.315
CBDLS635A	9.6	.378
CBDLS640A	11.2	.441
CBDLS645A	12.7	.500
CBDLS650A	14	.551
CBDLS655A	16	.630
CBDLS660A	18	.709
CBDLS665A	19.1	.752

TO SNAP LOCK IN A 3.5 (.137) Ø HOLE, IN  
A 0.8 - 2 (.031 - .078) PANEL THICKNESS



TO SNAP LOCK IN A 3.5 (.137) Ø HOLE, IN  
A 0.8 - 2 (.031 - .078) PANEL THICKNESS

TOLERANCES  
UNLESS NOTED  
≤ 5 mm ±0.2  
5 - 20 mm ±0.3  
20 - 40 mm ±0.4  
40 - 60 mm ±0.5  
60 - 100 mm ±0.8  
≥ 100 mm ±1.0

TITLE:

DUAL LOCKING CIRCUIT BOARD SUPPORT

FILE: CBDLS6XX

DWN: CLC

SHEET: 1 OF 1

SHEET SIZE: A

DT: 01/08/15

RE:



PART #

SEE TABLE

PRINT TYPE

CA



DWG IN  
MM (IN)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Essentra:

[CBDLS645A](#) [CBDLS615A](#) [CBDLS625A](#) [CBDLS630A](#) [CBDLS660A](#) [CBDLS620A](#) [CBDLS650A](#) [CBDLS610A](#)  
[CBDLS655A](#) [CBDLS640A](#) [CBDLS635A](#) [CBDLS605A](#) [CBDLS665A](#)