


Material: UL94 V-2 Nylon 6/6		
Color: Natural		
Part No.	A	
	mm	in
CBLS205A	3.2	.126
CBLS210A	4.8	0.187
CBLS215A	6.3	.248
CBLS220A	8	.315
CBLS225A	10	.394
CBLS230A	12	.472
CBLS235A	14	.551
CBLS240A	16	.630
CBLS245A	18	.709
CBLS250A	25	.984

TO SNAP LOCK IN A 3 (.118) Ø HOLE, IN A
1.2 - 1.7 (.047 - .067) PANEL THICKNESS



TO SNAP LOCK IN A 4.8 (.187) Ø HOLE, IN
A 0.8 - 2.2 (.031 - .086) PANEL THICKNESS

TOLERANCES
UNLESS NOTED
≤ 5 mm ±0.2
5 - 20 mm ±0.3
20 - 40 mm ±0.4
40 - 60 mm ±0.5
60 - 100 mm ±0.8
≥ 100 mm ±1.0

TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT					DWG IN MM (IN)	
	FILE: CBL2XX		DWN: CLC		PART # SEE TABLE	PRINT TYPE CA
	SHEET: 1 OF 1	SHEET SIZE: A	DT: 01/08/15			
	RE:		 ESSENTRA COMPONENTS			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBLS230A](#) [CBLS205A](#) [CBLS210A](#) [CBLS215A](#) [CBLS220A](#) [CBLS225A](#) [CBLS235A](#) [CBLS240A](#) [CBLS245A](#)
[CBLS250A](#)