


Material: UL94 V-2 Nylon 6/6		
Color: Natural		
Part No.	A	
	mm	in
CBLSP205A	3	.118
CBLSP210A	4	.157
CBLSP215A	6	.236
CBLSP220A	8	.315
CBLSP225A	10	.394
CBLSP230A	12	.472
CBLSP235A	14	.551
CBLSP240A	16	.630
CBLSP245A	18	.709

TO SNAP LOCK IN A 4 (.156) Ø HOLE, IN A
1.6 (.062) PANEL THICKNESS



TO SNAP LOCK IN A 4 (.156) Ø HOLE, IN A
1.6 (.062) PANEL THICKNESS

TOLERANCES
UNLESS NOTED
≤ 5 mm ±0.2
5 - 20 mm ±0.3
20 - 40 mm ±0.4
40 - 60 mm ±0.5
60 - 100 mm ±0.8
≥ 100 mm ±1.0

TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT					DWG IN MM (IN)	PRINT TYPE CA
	FILE: CBLSP2XX	DWN: CLC		PART #	SEE TABLE	
	SHEET: 1 OF 1	SHEET SIZE: A	DT: 01/08/15			
	RE:					
						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBLSP205A](#) [CBLSP210A](#) [CBLSP215A](#) [CBLSP220A](#) [CBLSP225A](#) [CBLSP230A](#) [CBLSP235A](#) [CBLSP240A](#)
[CBLSP245A](#)