


Material: UL94 V-2 Nylon 6/6			
Color: Natural			
Part No.	A		
	mm	in	
CBRLDS205A	3.5	.138	
CBRLDS210A	4.8	.189	
CBRLDS215A	6.4	.252	
CBRLDS220A	7	.276	
CBRLDS225A	8	.315	
CBRLDS230A	10	.394	
CBRLDS235A	11	.433	
CBRLDS240A	12.7	.500	
CBRLDS245A	15.9	.626	

TO SNAP LOCK IN A 3.5 (.137) Ø HOLE, IN
A 1.6 (.062) PANEL THICKNESS



TO SNAP LOCK IN A 5.5 (.216) Ø HOLE, IN A
0.8 - 1.6 (.031 - .062) PANEL THICKNESS

TOLERANCES
UNLESS NOTED

≤ 5 mm	±0.2
5 - 20 mm	±0.3
20 - 40 mm	±0.4
40 - 60 mm	±0.5
60 - 100 mm	±0.8
≥ 100 mm	±1.0

TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT		DWG IN MM (IN)	
FILE# CBR LDS2XX		PART #	
SHEET: 1 OF 1	SHEET SIZE: A	DT: 01/08/15	
RE:		PRINT TYPE	
		SEE TABLE	
		CA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBRLDS210A](#) [CBRLDS225A](#) [CBRLDS240A](#) [CBRLDS230A](#) [CBRLDS245A](#) [CBRLDS235A](#) [CBRLDS220A](#)
[CBRLDS215A](#) [CBRLDS205A](#)