


Material: UL94 V-2 Nylon 6/6		
Color: Natural		
Part No.	A	
	mm	in
CBRLDS305A	3.5	.138
CBRLDS310A	4.8	.189
CBRLDS315A	6.4	.252
CBRLDS320A	7	.276
CBRLDS325A	8	.315
CBRLDS330A	10	.394
CBRLDS335A	11	.433
CBRLDS340A	12.7	.500
CBRLDS345A	15.9	.626

TO SNAP LOCK IN A 3 (.118) Ø HOLE, IN A
1.6 (.062) PANEL THICKNESS



TO SNAP LOCK IN A 5.5 (.216) Ø HOLE, IN A
0.8 - 1.6 (.031 - .062) PANEL THICKNESS

TOLERANCES
UNLESS NOTED
≤ 5 mm ±0.2
5 - 20 mm ±0.3
20 - 40 mm ±0.4
40 - 60 mm ±0.5
60 - 100 mm ±0.8
≥ 100 mm ±1.0

TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT		DWG IN MM (IN)	
FILE# CBR LDS3XX		PART #	
SHEET: 1 OF 1		DT: 01/08/15	
RE:		PRINT TYPE	
ESSENTRA COMPONENTS		SEE TABLE CA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBRLDS325A](#) [CBRLDS340A](#) [CBRLDS310A](#) [CBRLDS345A](#) [CBRLDS330A](#) [CBRLDS315A](#) [CBRLDS335A](#)
[CBRLDS320A](#) [CBRLDS305A](#)