


| PART NUMBER<br>STYLE 1 | A    |
|------------------------|------|
| CBTS005A               | 4    |
| CBTS010A               | 5    |
| CBTS015A               | 6    |
| CBTS020A               | 7    |
| CBTS030A               | 9    |
| CBTS035A               | 9.5  |
| CBTS060A               | 12.7 |
| CBTS065A               | 13.5 |
| CBTS075A               | 15   |
| CBTS085A               | 17   |
| CBTS090A               | 18   |
| CBTS095A               | 19   |
| CBTS100A               | 20   |
| CBTS105A               | 22   |
| CBTS110A               | 24   |
| CBTS115A               | 25   |
| CBTS120A               | 27   |




M3x0.5 TAPPED

STYLE 1



M3x0.5 TAPPED



M3x0.5 TAPPED

STYLE 2

| PART NUMBER<br>STYLE 2 | A  |
|------------------------|----|
| CBTS130A               | 32 |
| CBTS135A               | 38 |
| CBTS140A               | 40 |
| CBTS145A               | 42 |
| CBTS150A               | 45 |
| CBTS155A               | 49 |
| CBTS160A               | 52 |

NOTES:

1. MATERIAL: UL 94 V-2 NYLON 6/6
2. COLOR: NATURAL

|      |                       |                 |
|------|-----------------------|-----------------|
| A    | INITIAL PRINT RELEASE | D.Z. 08/30/2019 |
| REV. | DESCRIPTION           | ENGR. DATE      |

|                                                                                      |               |                                                                                                                     |                |              |                            |
|--------------------------------------------------------------------------------------|---------------|---------------------------------------------------------------------------------------------------------------------|----------------|--------------|----------------------------|
| TITLE: <b>HEX THREADED STANDOFF</b>                                                  |               |                                                                                                                     |                | UNITS:<br>mm |                            |
| CREATED USING<br>SOLIDWORKS                                                          | FILE #: CBTS  | DWN: D.Z.                                                                                                           | APP: -         | FINAL        |                            |
| TOLERANCES<br>UNLESS NOTED<br>X<10=±0.2<br>10≤X<30=±0.3<br>30≤X<50=±0.5<br>X≥50=±0.7 | SHEET: 1 OF 1 | SHEET SIZE: A                                                                                                       | DT: 08/29/2019 | CHKD: -      | PART #                     |
| RE: --                                                                               | --            |  <b>ESSENTRA</b><br>COMPONENTS |                | SEE TABLES   | PRINT<br>TYPE<br><b>CA</b> |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Essentra:

[CBTS110A](#) [CBTS155A](#) [CBTS140A](#) [CBTS035A](#) [CBTS005A](#) [CBTS095A](#) [CBTS060A](#) [CBTS010A](#) [CBTS015A](#)  
[CBTS020A](#) [CBTS030A](#) [CBTS065A](#) [CBTS075A](#) [CBTS145A](#) [CBTS150A](#) [CBTS160A](#) [CBTS090A](#) [CBTS105A](#)  
[CBTS115A](#) [CBTS120A](#) [CBTS130A](#) [CBTS135A](#)