


Part No.	A	B	C
CF001A	7.4 ± 0.4	10.2 ± 0.4	2.64 ± 0.5
CF002A	10.7 ± 0.4	14.1 ± 0.4	2.04 ± 0.5
CF003A	10.7 ± 0.4	16 ± 0.4	3.3 ± 0.5
CF004A	13.8 ± 0.4	17.5 ± 0.4	3.1 ± 0.5
CF005A	14.1 ± 0.4	20 ± 0.4	3.7 ± 0.5
CF006A	17.2 ± 0.4	22 ± 0.4	3.1 ± 0.5
CF007A	18.3 ± 0.4	25 ± 0.4	4.1 ± 0.5
CF008A	21.2 ± 0.4	25.8 ± 0.4	3.1 ± 0.5
CF009A	24.3 ± 0.4	32 ± 0.4	3.61 ± 0.5
CF010A	28.7 ± 0.4	34 ± 0.4	3.1 ± 0.5
CF011A	31.2 ± 0.4	40 ± 0.4	4.12 ± 0.5
CF012A	34.9 ± 0.4	42 ± 0.4	3.1 ± 0.5
CF013A	40 ± 0.5	48 ± 0.5	2.85 ± 0.5
CF014A	39.6 ± 0.5	50 ± 0.5	4.85 ± 0.5



Material: PE
Color: GREY

TITLE: CF						UNITS: mm	
FILE #:		DWN: CLC	APP: -		PRELIMINARY		
SHEET: 1 OF 1		SHEET SIZE: A	DT: 08.27.2015		CHKD: -		PART #
RE:				ESSENTRA COMPONENTS			
REV.	DESCRIPTION	ENGR.	DATE				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CF001A](#) [CF002A](#) [CF003A](#) [CF004A](#) [CF005A](#) [CF006A](#) [CF007A](#) [CF008A](#) [CF009A](#) [CF010A](#) [CF011A](#) [CF012A](#)
[CF013A](#) [CF014A](#)