


PART NO.	DIM. "A" ±.015 (±0.4)
DLMSPM-2-01	1/8 (3.2)
DLMSPM-3-01	3/16 (4.8)
DLMSPM-4-01	1/4 (6.4)
DLMSPM-5-01	5/16 (7.9)
DLMSPM-6-01	3/8 (9.5)
DLMSPM-7-01	7/16 (11.1)
DLMSPM-8-01	1/2 (12.7)
DLMSPM-9-01	9/16 (14.3)
DLMSPM-10-01	5/8 (15.9)
DLMSPM-12-01	3/4 (19.1)
DLMSPM-13-01	13/16 (20.6)
DLMSPM-14-01	7/8 (22.2)
DLMSPM-16-01	1 (25.4)
DLMSPM-18-01	1-1/8 (28.6)
DLMSPM-20-01	1-1/4 (31.8)
DLMSPM-22-01	1-3/8 (34.9)
DLMSPM-24-01	1-1/2 (38.1)



NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01).
FLAME RETARDANT, NYLON (RMS-19).
AVAILABLE BY SPECIAL ORDER ONLY.
2. COLOR: NATURAL.

			TITLE: DUAL LOCKING MINI SUPPORT POST, MICRO						DWG IN IN (MM)	
D	CHANGED FILE NO. AND TITLE BLOCK	SM 05.03.01	TOLERANCES UNLESS NOTED	FILE # DLMSPM	DWN: P.B.	APP:	FINAL			
C	MAT'L RMS-19 ADDED	J.L. 12.29.97	.XX=±.010	MAT'L: SEE NOTES	DT: 03-07-95	DT:	PART #		PRINT TYPE CA	
B	P/N DLMSPM-13-01 ADDED	RT 11.06.96	.XXX=±.005	RE: RICHCO, INC.	RICHCO INC.		SEE TABLE			
A	P/N DLMSPM-9-01 ADDED	PB 07.24.95	FRAC=±1/64		PO BOX 804238, CHICAGO, 60680					
REV	DESCRIPTION	ENGR DATE	ANG=±1°	(773) 539-4060						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[DLMSPM-22-01](#) [DLMSPM-9-01](#) [DLMSPM-24-01](#) [DLMSPM-2-01](#) [DLMSPM-10-01](#) [DLMSPM-12-01](#) [DLMSPM-13-01](#)
[DLMSPM-14-01](#) [DLMSPM-16-01](#) [DLMSPM-18-01](#) [DLMSPM-20-01](#) [DLMSPM-3-01](#) [DLMSPM-4-01](#) [DLMSPM-5-01](#)
[DLMSPM-6-01](#) [DLMSPM-7-01](#) [DLMSPM-8-01](#)