



TO SNAP-LOCK IN A .152 (3.86)
 $\pm .002$ (0.05) DIA. HOLE, IN A
 .062 (1.57) THICK BOARD/CHASSIS
 (BOTH ENDS)

PART NO.	DIM. "A" $\pm .015$ (0.4)
DLMSP-2-01	1/8 (3.2)
DLMSP-3-01	3/16 (4.8)
DLMSP-4-01	1/4 (6.4)
DLMSP-5-01	5/16 (7.9)
DLMSP-6-01	3/8 (9.5)
DLMSP-7-01	7/16 (11.1)
DLMSP-8-01	1/2 (12.7)
DLMSP-9-01	9/16 (14.3)
DLMSP-10-01	5/8 (15.9)
DLMSP-12-01	3/4 (19.1)
DLMSP-14-01	7/8 (22.2)
DLMSP-16-01	1 (25.4)
DLMSP-18-01	1-1/8 (28.6)
DLMSP-20-01	1-1/4 (31.8)
DLMSP-22-01	1-3/8 (34.9)
DLMSP-24-01	1-1/2 (38.1)

NOTES:

- MAT'L: NYLON 66 (RMS-01).
 FLAME RETARDANT: NYLON (RMS-19),
 BY SPECIAL ORDER.
- COLOR: NATURAL.

			TITLE: DUAL LOCKING MINI SUPPORT POST						DWG IN IN (MM)	
D	CHANGED FILE NUMBER	SM 05.01.01	TOLERANCES UNLESS NOTED	FILE # DLMSP	DWN: P.B.	APP:	FINAL			
C	MAT'L RMS-19 ADDED	J.L. 12.29.97	.XX=±.010	MAT'L: SEE NOTES	DT: 04-07-95	DT:	PART # SEE TABLE		PRINT TYPE CA	
B	TITLE WAS MINI-SUPPORT POST, SPECIAL	PB 05.09.95	.XXX=±.005	RE: RICHCO, INC.	RICHCO INC.					
A	CONVERTED TO ACAD	PB 04.07.95	FRAC=±1/64	PO BOX 804238, CHICAGO, 60680						
REV	DESCRIPTION	ENGR DATE	ANG=±1°	(773) 539-4060						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[DLMSP-14-01](#) [DLMSP-10-01](#) [DLMSP-12-01](#) [DLMSP-16-01](#) [DLMSP-18-01](#) [DLMSP-20-01](#) [DLMSP-6-01](#) [DLMSP-7-01](#) [DLMSP-8-01](#) [DLMSP-9-01](#) [DLMSP-2-01](#) [DLMSP-22-01](#) [DLMSP-24-01](#) [DLMSP-3-01](#) [DLMSP-4-01](#) [DLMSP-5-01](#)