





PART NO.	"A" ±0.4 mm
DLSP-3-3M-01	3.0 mm
DLSP-3-4M-01	4.0 mm
DLSP-3-6M-01	6.0 mm
DLSP-3-8M-01	8.0 mm
DLSP-3-10M-01	10.0 mm
DLSP-3-12M-01	12.0 mm
DLSP-3-14M-01	14.0 mm
DLSP-3-16M-01	16.0 mm
DLSP-3-18M-01	18.0 mm



NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01)
FLAME RETARDANT, NYLON (RMS-19),
AVAILABLE BY SPECIAL ORDER ONLY.
2. COLOR: NATURAL.

			TITLE: DUAL LOCKING SUPPORT POST (METRIC) TYPE 3						DWG IN METRIC	
E	ADDED DIM. 3.15 AND TOL. TO DIM. 3.7	SM 05.28.02	TOLERANCES UNLESS NOTED X.X=±0.25 X.XX=±0.13 FRAC=±1/64 ANG=±1°	FILE # DLSP-3	DWN: P.B.	APP:	FINAL			
D	CHANGED FILE NUMBER	SM 06.19.01		MAT'L: SEE NOTES	DT: 10-04-94	DT:	PART #			
C	Tol.±.08 added to dim 4.0 mm	JL 4.3.00	RE: RICHCO, INC. RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060				SEE TABLE			PRINT TYPE CA
B	NOTE 2 REMOVED; 2ND CHART ADDED; DIM SEE CHART ADDED; DIM .24 (6) ADDED	PB 07.05.95								
A	-01 ADDED TO P/N'S	PB 11.09.94								
REV	DESCRIPTION	ENGR DATE								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[DLSP-3-10M-01](#) [DLSP-3-14M-01](#) [DLSP-3-3M-01](#) [DLSP-3-4M-01](#) [DLSP-3-6M-01](#) [DLSP-3-8M-01](#)