





TYPICAL APPLICATION



MOUNTING HOLE

PART NO.	"A"
EG-0-01	1/32 (0.8)
EG-1-01	1/16 (1.6)
EG-2-01	1/8 (3.2)
EG-3-01	3/16 (4.8)
EG-4-01	1/4 (6.4)
EG-5-01	5/16 (7.9)
EG-6-01	3/8 (9.5)
EG-7-01	7/16 (11.1)
EG-8-01	1/2 (12.7)

NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01).
FLAME RETARDANT, NYLON (RMS-19),
AVAILABLE BY SPECIAL ORDER ONLY.
2. COLOR: NATURAL.

2. COLOR: NATURAL.

			TITLE: EXPANSION GROMMET						DWG IN IN (MM)			
			TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°		FILE # EG-X		DWN: J.B.		APP:		FINAL	
					MAT'L: SEE NOTES		DT: 08-01-97		DT:		PART #	
I SEE ECN #564 FOR CHANGES SM 01.23.03					RE: RICHCO INC		RICHCO INC. PO BOX 804238,CHICAGO,60680 (773) 539-4060				SEE TABLE	
H UPDATED PRINT AND CHANGED FILE NO. SM 05.13.02											PRINT TYPE	
- SEE ENGINEERING FOR REV A-G -											CA	
REV DESCRIPTION ENGR DATE												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[EG-5-01](#) [EG-0-01](#) [EG-1-01](#) [EG-2-01](#) [EG-3-01](#) [EG-4-01](#) [EG-6-01](#) [EG-7-01](#) [EG-8-01](#)