



Open Hole Grommet, Black, Rubber, .250 in ID, .563 in OD, .250 in Thick, .375 in Hole Dia

In Stock !

Item Code: GR3165A

Black Rubber Hole Grommet convert raw-edged .250 in (6.4 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.

Description		Quantity	Unit Price	Options
Type	: Hole Grommet	Standard Pack: 6000		1 Add to Cart Request CAD Free Sample Request Quote
Compatible Hole Diameter	: .375 in (9.5 mm)	Order any quantity		
Inside Diameter	: .250 in (6.4 mm)	1	: \$0.6938	
Panel Thickness	: .063 in (1.6 mm)	50	: \$0.3384	
Color	: Black	1000	: \$0.1697	
Material	: Rubber	1500	: \$0.1082	
Overall Diameter	: .563 in (14.3 mm)	3000	: \$0.0769	
Overall Height	: .250 in (6.4 mm)	6000	: \$0.0616	
Hole Diameter	: .375 in (9.5 mm)	18000	: \$0.0586	
Full Material	: SBR	30000	: \$0.0555	
		42000	: \$0.0524	

[Print Page](#)

Dependent Products



Standard Cable Ties
- Locking, Nylon



Standard Cable Ties
- Locking, Weather
Resistant



Open Grommets -
Hole Grommets



Hook & Loop -
Standard Cable Ties

Help us improve our site

[Sign me up!](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[GR3165A](#)