



Open Hole Grommet, Black, Rubber, 1.500 in ID, 2.125 in OD, .500 in Thick, 1.750 in Hole Dia

In Stock !

Item Code: GR3163A

Black Rubber Hole Grommet convert raw-edged 1.500 in (38.1 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.

Description		Quantity	Unit Price	Options
Type	: Hole Grommet	Standard Pack: 600		1 Add to Cart Request CAD Free Sample Request Quote
Compatible Hole Diameter	: 1.750 in (44.5 mm)	Order any quantity		
Inside Diameter	: 1.500 in (38.1 mm)	1	: \$6.5033	
Panel Thickness	: .125 in (3.2 mm)	25	: \$3.1721	
Color	: Black	250	: \$1.5914	
Material	: Rubber	300	: \$1.0121	
Overall Diameter	: 2.125 in (54 mm)	600	: \$0.5782	
Overall Height	: .500 in (12.7 mm)	1800	: \$0.5485	
Hole Diameter	: 1.750 in (44.5 mm)	3000	: \$0.5198	
Full Material	: SBR	4200	: \$0.491	

[Print Page](#)

Dependent Products



Standard Cable Ties
- Locking, Nylon



Standard Cable Ties
- Locking, Weather
Resistant



Open Grommets -
Hole Grommets



Hook & Loop -
Standard Cable Ties

Recently Viewed

Help us improve our site

[Sign me up!](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[GR3163A](#)