



Open Hole Grommet, Black, Rubber, .875 in ID, 1.625 in OD, .625 in Thick, 1.250 in Hole Dia

In Stock !

Item Code: GR3118A

Black Rubber Hole Grommet convert raw-edged .875 in (22.2 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.

Description		Quantity	Unit Price	Options
Type	: Hole Grommet	Standard Pack: 800		1 Add to Cart Request CAD Free Sample Request Quote
Compatible Hole Diameter	: 1.250 in (31.8 mm)	Order any quantity		
Inside Diameter	: .875 in (22.2 mm)	1	: \$5.4106	
Panel Thickness	: .250 in (6.4 mm)	25	: \$2.6416	
Color	: Black	250	: \$1.3261	
Material	: Rubber	400	: \$0.8424	
Overall Diameter	: 1.625 in (41.3 mm)	800	: \$0.4806	
Overall Height	: .625 in (15.9 mm)	2400	: \$0.4562	
Hole Diameter	: 1.250 in (31.8 mm)	4000	: \$0.4328	
Full Material	: SBR	5600	: \$0.409	

[Print Page](#)

Dependent Products



Cable Clamps -
Screw Mount, Wire
Harness



Open Grommets -
Hole Grommets



Standard Cable Ties
- Locking, Nylon



Cable Clamps -
Adhesive Mount,
Adjustable

Help us improve our site

[Sign me up!](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[GR3118A](#)