



Open Hole Grommet, Black, Rubber, .250 in ID, .625 in OD, .313 in Thick, .438 in Hole Dia

In Stock !

Item Code: GR3127A

Black Rubber Hole Grommet convert raw-edged .250 in (6.4 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.

Description		Quantity	Unit Price	Options
Type	: Hole Grommet	Standard Pack: 2500 Order any quantity		1 Add to Cart Request CAD Free Sample Request Quote
Compatible Hole Diameter	: .438 in (11.1 mm)			
Inside Diameter	: .250 in (6.4 mm)	1	: \$1.0927	
Panel Thickness	: .188 in (4.8 mm)	50	: \$0.5347	
Color	: Black	500	: \$0.2673	
Material	: Rubber	625	: \$0.1697	
Overall Diameter	: .625 in (15.9 mm)	1250	: \$0.1209	
Overall Height	: .313 in (8 mm)	2500	: \$0.0972	
Hole Diameter	: .438 in (11.1 mm)	7500	: \$0.0924	
Full Material	: SBR	12500	: \$0.0875	
		17500	: \$0.0826	

[Print Page](#)

Dependent Products



Cable Clamps -
Screw Mount, Wire
Harness



Open Grommets -
Hole Grommets



Standard Cable Ties
- Locking, Nylon



Cable Clamps -
Adhesive Mount,

Help us improve our site

[Sign me up!](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[GR3127A](#)