



Open Hole Grommet, Black, Rubber, .500 in ID, 1.063 in OD, .438 in Thick, .813 in Hole Dia

In Stock !

Item Code: GR3132A

Black Rubber Hole Grommet convert raw-edged .500 in (12.7 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.

Description		Quantity	Unit Price	Options
Type	: Hole Grommet	Standard Pack: 2000		1 Add to Cart Request CAD Free Sample Request Quote
Compatible Hole Diameter	: .813 in (20.7 mm)	Order any quantity		
Inside Diameter	: .500 in (12.7 mm)	1	: \$2.7053	
Panel Thickness	: .188 in (4.8 mm)	50	: \$1.3261	
Color	: Black	250	: \$0.6599	
Material	: Rubber	500	: \$0.4201	
Overall Diameter	: 1.063 in (27 mm)	1000	: \$0.3002	
Overall Height	: .438 in (11.1 mm)	2000	: \$0.2408	
Hole Diameter	: .813 in (20.7 mm)	6000	: \$0.2281	
Full Material	: SBR	10000	: \$0.216	
		14000	: \$0.204	

[Print Page](#)

Dependent Products



Cable Clamps -
Screw Mount, Wire
Harness



Open Grommets -
Hole Grommets



Standard Cable Ties
- Locking, Nylon



Cable Clamps -
Adhesive Mount,

Help us improve our site

[Sign me up!](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[GR3132A](#)