



Open Hole Grommet, Black, Rubber, 1.500 in ID, 2.125 in OD, .750 in Thick, 1.750 in Hole Dia

In Stock !

Item Code: GR3295A

Black Rubber Hole Grommet convert raw-edged 1.500 in (38.1 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.

Description		Quantity	Unit Price	Options
Type	: Hole Grommet	Standard Pack: 300		1 Add to Cart Request CAD Free Sample Request Quote
Compatible Hole Diameter	: 1.750 in (44.5 mm)	Order any quantity		
Inside Diameter	: 1.500 in (38.1 mm)	1	: \$9.7178	
Panel Thickness	: .375 in (9.5 mm)	25	: \$4.7528	
Color	: Black	100	: \$2.3764	
Material	: Rubber	150	: \$1.5065	
Overall Diameter	: 2.125 in (54 mm)	300	: \$0.8646	
Overall Height	: .750 in (19.1 mm)	900	: \$0.8211	
Hole Diameter	: 1.750 in (44.5 mm)	1500	: \$0.7787	
Full Material	: SBR	2100	: \$0.734	

[Print Page](#)

Dependent Products



Standard Cable Ties
- Locking, Nylon



Standard Cable Ties
- Locking, Weather
Resistant



Open Grommets -
Hole Grommets



Hook & Loop -
Standard Cable Ties

Recently Viewed

Help us improve our site

[Sign me up!](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[GR3295A](#)