



Open Hole Grommet, Black, Rubber, .688 in ID, 1.313 in OD, .375 in Thick, 1.000 in Hole Dia

In Stock !

Item Code: GR3068A

Black Rubber Hole Grommet convert raw-edged .688 in (17.5 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.

Description		Quantity	Unit Price	Options
Type	: Hole Grommet	Standard Pack: 1500		1 Add to Cart Request CAD Free Sample Request Quote
Compatible Hole Diameter	: 1.000 in (25.4 mm)	Order any quantity		
Inside Diameter	: .688 in (17.5 mm)	1	: \$3.5858	
Panel Thickness	: .063 in (1.6 mm)	50	: \$1.7505	
Color	: Black	250	: \$0.8763	
Material	: Rubber	500	: \$0.558	
Overall Diameter	: 1.313 in (33.4 mm)	750	: \$0.3989	
Overall Height	: .375 in (9.5 mm)	1500	: \$0.3183	
Hole Diameter	: 1.000 in (25.4 mm)	4500	: \$0.3034	
Full Material	: SBR	7500	: \$0.287	
		10500	: \$0.272	

[Print Page](#)

Dependent Products



Cable Clamps -
Screw Mount, Wire
Harness



Open Grommets -
Hole Grommets



Standard Cable Ties
- Locking, Nylon



Cable Clamps -
Adhesive Mount,

Help us improve our site

[Sign me up!](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[GR3068A](#)