



Open Hole Grommet, Black, Rubber, .375 in ID, .875 in OD, .313 in Thick, .625 in Hole Dia

In Stock !

Item Code: GR3076A

Black Rubber Hole Grommet convert raw-edged .375 in (9.5 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.

Description		Quantity	Unit Price	Options
Type	: Hole Grommet	Standard Pack: 5000 Order any quantity		1 Add to Cart Request CAD Free Sample Request Quote
Compatible Hole Diameter	: .625 in (15.9 mm)			
Inside Diameter	: .375 in (9.5 mm)	1	: \$1.8141	
Panel Thickness	: .063 in (1.6 mm)	50	: \$0.8922	
Color	: Black	500	: \$0.4456	
Material	: Rubber	1250	: \$0.2833	
Overall Diameter	: .875 in (22.2 mm)	2500	: \$0.2026	
Overall Height	: .313 in (8 mm)	5000	: \$0.1623	
Hole Diameter	: .625 in (15.9 mm)	15000	: \$0.1538	
Full Material	: SBR	25000	: \$0.145	
		35000	: \$0.138	

[Print Page](#)

Dependent Products



Standard Cable Ties
- Locking, Nylon



Standard Cable Ties
- Locking, Weather
Resistant



Open Grommets -
Hole Grommets



Hook & Loop -
Standard Cable Ties

Help us improve our site

[Sign me up!](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[GR3076A](#)