

1

2

3

4

A




B

C


D

E

F



REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	21/02/05	NJB
02	ECN 2005-032	02/03/05	NJB
03	ECN 2005-044	06/04/05	NJB
04	ECN 2007-209	23/11/07	NJB
05	ECN 2008-009	14/01/08	SF
06	CO2010138	11/03/08	SF
07	CO2010171	03/04/08	SF
08	CO2010206	01/05/08	SF



EXWHC2-750

EXWHC2-500

EXWHC2-250

NOTES

1) PARTS ARE AVAILABLE IN BLACK
ADD "BK" TO END OF PART NUMBER:
EXWHC2-500-01BK.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO
RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR
REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

PART No.	"A" HOLDING Ø	"B"	"C"	"D"	"E" REF	"F"	MATERIAL
EXWHC2-750-01	18.0[.708]	1.8[.070]	12.7[.500]	4.7[.185]	35.0[1.377]	6.35[.250]	NYLON 6/6 UL94 V-2 (RMS-01)
EXWHC2-750-19							NYLON 6/6 UL94 V-0 (RMS-19)
EXWHC2-500-01	12.7[.500]	1.6[.063]	10.0[.394]	30.0[1.181]	5.0[.196]	5.0[.196]	NYLON 6/6 UL94 V-2 (RMS-01)
EXWHC2-500-19							NYLON 6/6 UL94 V-0 (RMS-19)
EXWHC2-250-01	6.35[.250]	1.0[.039]	10.0[.394]	6.0[.236]	21.0[0.827]	5.0[.196]	NYLON 6/6 UL94 V-2 (RMS-01)
EXWHC2-250-19							NYLON 6/6 UL94 V-0 (RMS-19)



METRIC PRIMARY UNITS: mm
IMPERIAL SECONDARY UNITS: [inches]
GENERAL TOLERANCES ±0.25 [0.010]
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°



MATERIAL:

SEE TABLE

COLOUR:

NATURAL

DESCRIPTION:

WIRE HARNESS CLIP

PART No:

SEE TABLE

DRG No:

05-024

NPR No:

2007-436

SHEET SIZE

A4

DRN

NJB

DATE

21/02/05

CHKD

NBR

DATE

22/02/05

SCALE

NTS

SHEET No.

1 OF 1

A

B

C

D

E

FORM No. 0145/03

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[EXWHC2-250-01](#) [EXWHC2-500-01](#) [EXWHC2-750-01](#)