



PART NO.	MATERIAL	COLOR	ADHESIVE
FTH-10-01	NYLON 6/6 (RMS-01)	NATURAL	NONE
FTH-10A-RT			ACRYLIC TAPE (RMS-15), WHITE LINER

THESE BUMPS MAY NOT
APPEAR ON PART (8PLS)



ACCOMMODATES WIT-18 THRU WIT-120,
AND QTE-18 THRU QTE-120 TIES





OPTIONAL 1/32" (0.8)
DOUBLE ADHESIVE TAPE
WITH RELEASE TAB

NOTES:

1. NYLON 6/6 (RMS-01),
COLOR: NATURAL,
RUBBER ADHESIVE TAPE (RMS-102), BLUE LINER,
AVAILABLE BY SPECIAL ORDER ONLY;
TO ORDER USE P/N FTH-10A1-RT.

FLAME RETARDANT NYLON (RMS-19),
COLOR: NATURAL,
ACRYLIC ADHESIVE TAPE (RMS-15), WHITE LINER,
AVAILABLE BY SPECIAL ORDER ONLY;
TO ORDER USE P/N FTH-10A-RT-19
OR FTH-10-19 (WITHOUT TAPE).

UV STABILIZED NYLON (RMS-46),
COLOR: BLACK,
ACRYLIC ADHESIVE TAPE (RMS-15), WHITE LINER,
AVAILABLE BY SPECIAL ORDER ONLY;
TO ORDER USE P/N FTH-10A-RT-UVB
OR FTH-10-UVB (WITHOUT TAPE),
RUBBER ADHESIVE TAPE (RMS-102), BLUE LINER,
AVAILABLE BY SPECIAL ORDER ONLY.
TO ORDER USE P/N FTH-10A1-RT-UVB.

TITLE: FLAT TIE HOLDER					DWG IN IN (MM)	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE #	FTH-10	DWN: JL	APP:	FINAL	
	MAT'L:	SEE NOTES	DT: 01.10.00	DT:	PART #	PRINT TYPE
	RE:	RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		SEE TABLE	CA

E	SEE CO 200248 FOR CHANGES	SK 10.30.08
D	SEE ECN #1124 FOR CHANGES	SK 01.24.06
C	COMPLETELY RE-DRAWN & CHANGED FILE#	SM 10.18.01
B	ADDED (RMS-102) BY SPECIAL ORDER ONLY	JL 08.22.00
A	MAT'L NOTES UPDATED	JL 01.10.00
REV	DESCRIPTION	ENGR DATE

TOLERANCES
UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[FTH-10A-RT-M](#)