




NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01),  
COLOR NATURAL.
2. FLAME RETARDANT NYLON (RMS-19).  
COLOR NATURAL.  
AVAILABLE BY SPECIAL ORDER ONLY;  
TO ORDER USE P/N FTH-13R-19 OR FTH-13S-19.
3. UV STABILIZED NYLON 6/6 (RMS-46),  
COLOR BLACK.  
AVAILABLE BY SPECIAL ORDER ONLY;  
TO ORDER USE P/N FTH-13R-UVB OR FTH-13S-UVB.
4. MOUNTING SCREW FOR FTH-13R: NO. 8 (M4) PAN HEAD,  
MOUNTING SCREW FOR FTH-13S: NO. 8 (M4) FLAT HEAD OR  
NO. 6 (M3.5) FLAT, ROUND, OR PAN HEAD.

MOUNTING RIVETS FOR - FTH-13R		
USE RIVET NO.	HOLE DIA.	FOR PANEL THICKNESS RANGE
SR-4050	.161 (4.1)	.018-.058 (0.5-1.5)
SR-4060		.058-.097 (1.5-2.5)
SR-4070		.097-.137 (2.5-3.5)
SR-4080		.137-.176 (3.5-4.5)
SR-4100		.215-.255 (5.5-6.5)

NO. 8 (MS-3) FLAT, ROUND, OR PAN HEAD.			TITLE: FLAT TIE HOLDER						DWG IN IN (MM)		
D	SEE ECN #1124 FOR CHANGES	SK 01.24.06	TOLERANCES UNLESS NOTED	FILE # FTH-13X	DWN: E.P.	APP:	FINAL				
C	UPDATED PRINT AND CHANGED FILE NO.	SM 05.20.02	.XX=±.010	MAT'L: SEE NOTES	DT: 12-30-98	DT:	PART #		PRINT TYPE		
B	REDRAWN TO INCLUDE FTH-13S-01 DWG.	RG11/02/00	.XXX=±.005	RE: RICHCO, INC.	RICHCO INC.		FTH-13 SERIES		CA		
A	FR NYLON 66 (RMS-19) ADDED	JL 01.06.00	FRAC=±1/64		PO BOX 804238,CHICAGO,60680						
REV	DESCRIPTION	ENGR DATE	ANG=±1°								

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[FTH-13R-01-C](#) [FTH-13R-01-M](#) [FTH-13S-01-C](#) [FTH-13S-01-M](#)