



| | |
|-------------|--------------|
| PART NO. | "A"±.010 |
| LCBG-1-01 | .880 (22.4) |
| LCBG-1.5-01 | 1.375 (34.9) |
| LCBG-2-01 | 1.870 (47.5) |
| LCBG-3-01 | 2.875 (73.0) |



RECOMMENDED MOUNTING HOLE



BOARD THICKNESS: .030-.070 (0.76-1.78)

NOTES:

- MATERIAL: NYLON 6/6 (RMS-01).
FLAME RETARDANT NYLON (RMS-19).
AVAILABLE BY SPECIAL ORDER ONLY.
- COLOR: NATURAL.

| | | | | | | | | | | |
|--|--|--|------------------------------------|--|-------------------------------|--------------|----------------|-----------|------------|--|
| F CREATED SEPARATE DWG FOR LCBG-T SM. 12.03.01 | | | TITLE: LOCKING CIRCUIT BOARD GUIDE | | | | DWG IN IN (MM) | | FINAL | |
| E CHANGED FILE NUMBER SM 05.11.01 | | | TOLERANCES UNLESS NOTED | | FILE # LCBG | DWN: P.B. | APP: | | | |
| D P/N CHANGED FOR ALL LCBG-XT JL 12.30.99 | | | .XX=±.010 | | MAT'L: SEE NOTES | DT: 06-27-94 | DT: | PART # | | |
| C CORRECTED VARIOUS DIMS & TOLERANCES MO 1/16/98 | | | .XXX=±.005 | | RE: RICHCO, INC. | RICHCO INC. | | SEE NOTES | | |
| B MAT'L RMS-19 ADDED. J.L. 12.29.97 | | | FRAC=±1/64 | | PO BOX 804238, CHICAGO, 60680 | | | | PRINT TYPE | |
| A LCBG-xx-01 TOP ADDED. 01-15-97 | | | ANG=±1° | | (773) 539-4060 | | | | CA | |
| REV DESCRIPTION ENGR DATE | | | | | | | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[LCBG-3-01](#) [LCBG-1-01](#) [LCBG-2-01](#) [LCBG-1.5-01](#)