



M3 THREAD

PART NO.	"A"	
MTS-6	.25 (6.35)	±.010 (±0.25)
MTS-8	.31 (8.0)	
MTS-10S	.39 (10.0)	
MTS-10	.41 (10.5)	
MTS-11	.43 (11.0)	
MTS-12	.47 (12.0)	
MTS-13	.50 (12.8)	
MTS-14	.55 (14.0)	
MTS-16	.63 (16.0)	
MTS-18	.72 (18.2)	±.012 (.31)
MTS-20	.79 (20.1)	
MTS-30	1.18 (30.0)	±.014 (.36)

NOTES:

1. MATERIAL: NYLON 6/6.
FLAME RETARDANT NYLON (RMS-146),
AVAILABLE BY SPECIAL ORDER.
TO ORDER ADD "-146" AS SUFFIX.
2. COLOR: NATURAL.

TITLE: METRIC THREADED SPACER					DWG IN IN (MM)	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # MTS	DWN: P.B.	APP:	FINAL		
	MAT'L: SEE NOTES	DT: 07-24-95	DT:	PART #		PRINT
	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		SEE TABLE		TYPE
						CA

D	SEE CO 200041 FOR CHANGES	SK 09.28.07
C	SEE ECN #522 FOR CHANGES	SM 11.14.02
B	CHANGED FILE NUMBER	SM 05.11.01
A	REMOVED RMS-01	SM 02.09.01
REV	DESCRIPTION	ENGR DATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[MTS-14](#) [MTS-13](#) [MTS-10](#) [MTS-10S](#) [MTS-11](#) [MTS-12](#) [MTS-16](#) [MTS-18](#) [MTS-20](#) [MTS-30](#) [MTS-6](#) [MTS-8](#)