



TO SNAP-LOCK IN A 3 ± 0.05 [.118 $\pm$.002] HOLE DIA.,
IN A PANEL THICKNESS INDICATED

NYLON 6/6 UL 94 V-2 (RMS-01). COLOR: NATURAL. PART NO.	NYLON 6/6 UL 94 V-0 (RMS-19). COLOR: NATURAL. PART NO.	DIM. "A"	PANEL THICKNESS RANGE
MWSET2-1-01	MWSET2-1-19	4.29 [.169]	1-1.2 [.039-.047]
MWSET2-2-01	MWSET2-2-19	4.79 [.189]	1.2-1.6 [.047-.063]
MWSET2-3-01	MWSET2-3-19	5.05 [.199]	1.4-1.8 [.055-.071]
MWSET2-4-01	MWSET2-4-19	5.81 [.229]	2.2-2.6 [.087-.102]

NOTES:
1. ALTERNATE UNITS FOR REFERENCE ONLY

			TITLE: MICRO WIRE SADDLE, TEARDROP				 		DWG IN IN [MM]			
			CREATED USING SOLIDWORKS		FILE #: MWSET2-X		DWN: SK		APP: RT		FINAL	
			GENERAL TOLERANCE UNLESS NOTED		SHEET: 1 OF 1		SHEET SIZE: A		DT: 07/11/06		CHKD: DZ	
					RE: RICHCO, INC.		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		PART #		PRINT TYPE	
									SEE TABLE		CA	
							</					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[MWSET2-1-01](#) [MWSET2-1-19](#) [MWSET2-2-01](#) [MWSET2-2-19](#)