




NYLON 6/6 (RMS-01) COLOR: NATURAL. PART NO.	FLAME RET. (RMS-19) COLOR: NATURAL. PART NO.	DIM. "A" REF.	DIM. "B" REF.	HOLE DIA.	PANEL THICKNESS
MWS-1-01	MWS-1-19	.23 (5.8)	.12 (3.0)	.070±.002 (1.75±0.05)	.062 (1.57)
MWS1-1-01	MWS1-1-19				.093 (2.36)
----	MWS-2-19	.44 (11.2)	.33 (8.5)		.063 (1.60)
----	MWS-3-19				.087 (2.20)



SEE ECN #887 FOR CHANGES			SM 12.13.04	TITLE: MICRO WIRE SADDLE					DWG IN IN (MM)	
F	UPDATED PRINT AND CHANGED FILE NO.	SM 05.29.01	TOLERANCES UNLESS NOTED .XX=±.01 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # MWS	DWN: JL	DT: 07/26/00	FINAL			
D	REVISED TABLE	J.L 07.26.00		MAT'L: SEE TABLE	CHKD:	ENG:	PART #		PRINT TYPE CA	
C	MAT'L RMS-19 ADDED	J.L 12.10.97		RE: RICHCO, INC.		RICHCO INC.		SEE TABLE		
B	ADDED P/N MWS1 AND PUT IN CHART	JB 12.22.95				ENG@RICHCO-INC.COM				
A	CONVERTED TO ACAD	PB 10.21.94				(773) 539-4060				
REV	DESCRIPTION	ENGR DATE								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[MWS-1-01](#) [MWS1-1-01](#) [MWS1-1-19](#) [MWS-1-19](#) [MWS-2-19](#) [MWS-3-19](#)