

MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01). COLOR: NATURAL. PART NO.	MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01). COLOR: BLACK. PART NO.	DIM. "E" REF.	"D" HOLDING DIAMETER FOR:			FIGURE NO.
			INSIDE HOLE	CENTER HOLE	OUTSIDE HOLE	
N-20B	N-20B-BK	29/32 [23]	1 [25.4]	1-1/8 [28.6]	1.2 [30.2]	1
N-24B	N-24B-BK	1-1/32 [26.2]	1-1/4 [31.8]	1-3/8 [34.9]	1-15/32 [37.3]	
N-32B	N-32B-BK	1-29/64 [36.9]	1-3/4 [44.5]	1-7/8 [47.6]	2 [50.8]	2

FIG 1.





FIG 2.



NOTES:

1. MATERIAL: NYLON 6/6 UL 94 V-0 (RMS-19),
COLOR: NATURAL OR BLACK
AVAILABLE BY SPECIAL ORDER ONLY.

AVAILABLE BY SPECIAL ORDER ONLY.

TITLE: CABLE CLAMPS, NB SERIES-3 HOLES			  			
CREATED USING SOLIDWORKS	FILE #: NB-3		DWN: SK	APP: R.T.	FINAL	
TOLERANCES UNLESS NOTED	SHEET: 1 OF 1	SHEET SIZE: A	DT: 10/20/08	CHKD: D.Z.	PART #	PRINT TYPE
.XX=±.010	RE: RICHCO, INC.		RICHCO, INC.		SEE TABLE	CA
.XXX=±.005			ENG@RICHCO-INC.COM			
FRAC.=±1/64			(773) 539-4060			
ANG.=±1°						
F SEE ECN #200264 FOR CHANGES	SK	10/20/08				
- SEE ENGINEERING FOR REV A-F	-	----				
REV. DESCRIPTION	ENGR.	DATE				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[N-20B](#) [N-20B-BK](#) [N-24B](#) [N-24B-BK](#) [N-32B](#) [N-32B-BK](#)