



PART NO.	"D" <sup>+0.0 -0.1</sup>	"d" <sup>+0.2 -0.1</sup>	MATERIAL	"L"
*OFBLT-P-2.6-05-PP	5.05	2.6	POLYPROPYLENE, WHITE (RMS-86)	100 METERS
OFBLT-P-3.1-05-PP		3.1		
OFBLT-P-4.2-635-PP	6.35	4.2		
OFBLT-P-3.1-05-PBT V0	5.05	3.1	PBT V0, BLACK UL94-V0 RATED (RMS-140)	
*OFBLT-P-4.2-635-PBT V0	6.35	4.2		
OFBLT-P-2.6-05-PVDF	5.05	2.6	PVDF, NATURAL PLENUM RATED (RMS-141)	
OFBLT-P-3.1-05-PVDF		3.1		
OFBLT-P-4.2-635-PVDF	6.35	4.2		




\*PARTS AVAILABLE BY SPECIAL ORDER ONLY



# NOTES:

- PLENUM RATED TYPE  
AVAILABLE BY SPECIAL ORDER ONLY.

APPLICABLE PATENTS: CANADA PAT. NO.2122064  
AUSTRALIA PAT. NO. 29063/92  
EUROPE PAT. NO. 92923018.3  
USA PAT. NO. 5 473 723

AVAILABLE BY SPECIAL ORDER ONLY.			TITLE: OPTICAL FIBER BEND LIMITING TUBE, PULL CORD VERSION						DWG IN mm	
E	SEE CO 200035 FOR CHANGES	SK 09.26.07	TOLERANCES UNLESS NOTED	FILE # OFBLT-P	DWN: AM	APP:	FINAL			
D	SEE ECN #1012 FOR CHANGES	SK 06.03.05		MAT'L: SEE TABLE	DT: 5/14/99	DT:				
C	ADDED RMS NOTE TO TABLE	SJ 04.24.02	.XX= .XXX= FRAC= ANG=1°	RE: RICHCO, INC.	RICHCO INC.		PART #  SEE TABLE	PRINT TYPE CA		
B	REMOVED P/N: OFBLT-P-2.6-05-PBT V0	SM 02.05.02			PO BOX 804238, CHICAGO, 60680					
A	UPDATED PRINT, CHANGED FILE NO.	SM 01.31.02			(773) 539-4060					
REV	DESCRIPTION	ENGR DATE								

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[OFBLTP-42-635PP](#)