


PART NO.	"A" ±1/8" (±3.2)	"W" ±.125 (±3.2)	"L" ±.50 (±12.7)	PACKAGING
RKW-6-6	3/8 (9.5)	.75 (19.1)	6.0 (152.4)	100
RKW-8-6	1/2 (12.7)	1.0 (25.4)		
RKW-8-8			8.0 (203.2)	
RKW-8-11			11.0 (279.4)	
RKW-12-15	3/4 (19.1)	1.5 (38.1)	15.0 (381.0)	
RKW-12-18			18.0 (457.2)	
RKW-12-24			24.0 (609.6)	





NOTES:

1. MATERIAL: HOOK: LOW DENSITY POLYETHYLENE (RMS-249).
2. LOOP: NYLON KNIT (RMS-251).
3. OPERATING TEMP: 120°F.

TO ORDER COLORS ADD SUFFIX TO "PART NO."
 BLACK: -B, WHITE: -W, BLUE: -BL,
 RED: -RD, YELLOW: -YL,
 GREEN: -GN, ORANGE -OR.

OTHER COLORS AVAILABLE BY
SPECIAL ORDER.

F	SEE ECN #1263 FOR CHANGES	SK 12.12.06	TITLE: RICHCO KWIK WRAP					DWG IN IN (MM)	
E	SEE ECN #538 FOR CHANGES	SM 12.10.02	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE #	RKW	DWN: J.L.	APP:	FINAL	
D	REMOVED RKS-8-12 TO SAPARATE PRINT	SM 02.26.02		MAT'L: SEE NOTES		DT: 6.2.98	DT:	PART # SEE TABLE	PRINT TYPE CA
C	METRIC CONVERSION CORRECTED	DM 12.12.01		RE: RICHCO, INC. RICHCO INC. PO BOX 804238,CHICAGO,60680 (773) 539-4060					
B	CHANGED FILE NO.	DM 12.06.01							
A	CHANGED TABLE; ADDED 2 BASE PARTS & DIM "W".	SM 02.23.01							
REV	DESCRIPTION	ENGR DATE							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[RKW-12-18-W](#) [RKW-12-24-YL](#) [RKW-12-15-BK](#) [RKW-12-15-BK-C](#) [RKW-12-15-BL](#) [RKW-12-15-GN](#) [RKW-12-15-OR](#)
[RKW-12-15-RD](#) [RKW-8-9-W](#) [RKW-8-9-YL](#) [RKWPR-12-13](#) [RKWPR-6-6](#) [RKWPR-8-12](#) [RKWPR-8-8](#) [RKW-8-9-BK](#)
[RKW-8-9-BK-C](#) [RKW-8-9-BL](#) [RKW-8-9-GN](#) [RKW-8-9-OR](#) [RKW-8-9-RD](#) [RKW-8-8-BL](#) [RKW-8-8-GN](#) [RKW-8-8-OR](#)
[RKW-8-8-RD](#) [RKW-8-8-W](#) [RKW-8-8-YL](#) [RKW-8-6-OR](#) [RKW-8-6-RD](#) [RKW-8-6-W](#) [RKW-8-6-YL](#) [RKW-8-8-BK](#) [RKW-](#)
[8-8-BK-C](#) [RKW-8-13-W](#) [RKW-8-13-YL](#) [RKW-8-6-BK](#) [RKW-8-6-BK-C](#) [RKW-8-6-BL](#) [RKW-8-6-GN](#) [RKW-8-13-BK](#)
[RKW-8-13-BK-C](#) [RKW-8-13-BL](#) [RKW-8-13-GN](#) [RKW-8-13-OR](#) [RKW-8-13-RD](#) [RKW-8-12-BL](#) [RKW-8-12-GN](#) [RKW-](#)
[8-12-OR](#) [RKW-8-12-RD](#) [RKW-8-12-W](#) [RKW-8-12-YL](#) [RKW-8-11-OR](#) [RKW-8-11-RD](#) [RKW-8-11-W](#) [RKW-8-11-YL](#)
[RKW-8-12-BK](#) [RKW-8-12-BK-C](#) [RKW-6-6-W](#) [RKW-6-6-YL](#) [RKW-8-11-BK](#) [RKW-8-11-BK-C](#) [RKW-8-11-BL](#) [RKW-8-](#)
[11-GN](#) [RKW-6-6-BK](#) [RKW-6-6-BK-C](#) [RKW-6-6-BL](#) [RKW-6-6-GN](#) [RKW-6-6-OR](#) [RKW-6-6-RD](#) [RKW-12-9-BL](#) [RKW-](#)
[12-9-GN](#) [RKW-12-9-OR](#) [RKW-12-9-RD](#) [RKW-12-9-W](#) [RKW-12-9-YL](#) [RKW-12-24-GN](#) [RKW-12-24-OR](#) [RKW-12-24-](#)
[RD](#) [RKW-12-24-W](#) [RKW-12-9-BK](#) [RKW-12-9-BK-C](#) [RKW-12-18-OR](#) [RKW-12-18-RD](#) [RKW-12-18-YL](#) [RKW-12-24-](#)
[BK](#) [RKW-12-24-BK-C](#) [RKW-12-24-BL](#) [RKW-12-15-W](#) [RKW-12-15-YL](#) [RKW-12-18-BK](#) [RKW-12-18-BK-C](#) [RKW-12-](#)
[18-BL](#) [RKW-12-18-GN](#)