


PART NO.	DIM. "A"±.016 (±0.41)	DIM. B"±.016 (±0.41)
RSSHG-201-165	2.0 (50.8)	1.0 (25.4)
RSSHG-251-165	2.5 (63.5)	1.5 (38.1)
RSSHG-301-165	3.0 (76.2)	2.0 (50.8)
RSSHG-351-165	3.5 (88.9)	2.5 (63.5)
RSSHG-401-165	4.0 (101.6)	3.0 (76.2)
RSSHG-451-165	4.5 (114.3)	3.5 (88.9)
RSSHG-501-165	5.0 (127.0)	4.0 (101.6)
RSSHG-551-165	5.5 (139.7)	4.5 (114.3)
RSSHG-601-165	6.0 (152.4)	5.0 (127.0)



NOTES:

1. MATERIAL: FLAME RETARDANT NYLON 6/6 (RMS-66).
2. COLOR: BLACK.

TITLE: SINGLE SIDED HORIZONTAL CARD GUIDE			DWG IN (MM) FINAL		PRINT TYPE CA
TOLERANCES UNLESS NOTED .XX=±.01 (X.XX)=±0.5	FILE # RSSHG	DWN: SM	DT: 12/17/01	PART #	
	MAT'L: SEE NOTES	CHKD:	ENGR: RT	SEE TABLE	
	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060			
B SEE ECN #874 FOR CHANGES	SM 10.27.04				
A REDRAWN FROM UK PRINT (REV. A)	SM 12.17.01				
REV DESCRIPTION	ENGR DATE				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[RSSHG-301-165](#)