



NYLON 6/6 (RMS-01) COLOR: NATURAL	FLAME RETARDANT (RMS-19) COLOR: NATURAL	"A" $\pm .015$ (± 0.4)
SCBS-4-01	SCBS-4-19	1/4 (6.4)
SCBS-6-01	SCBS-6-19	3/8 (9.5)
SCBS-8-01	SCBS-8-19	1/2 (12.7)
SCBS-10-01	SCBS-10-19	5/8 (15.9)
SCBS-12-01	SCBS-12-19	3/4 (19.1)
SCBS-14-01	SCBS-14-19	7/8 (22.2)
SCBS-16-01	SCBS-16-19	1 (25.4)
SCBS-18-01	SCBS-18-19	1-1/8 (28.6)
SCBS-22.5-01	SCBS-22.5-19	1-13/32 (35.7)

			TITLE: STUDDED CIRCUIT BOARD SUPPORT						DWG IN IN (MM)			
			TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°		FILE # SCBS		DWN: PB/JB		APP:		FINAL	
					MAT'L: SEE TABLE		DT: 10-02-95		DT:		PART #	
C SEE ECN #512 FOR CHANGES SM 11.08.02					RE: RICHCO, INC.		RICHCO INC.		PO BOX 804238,CHICAGO,60680		SEE TABLE	
B CHANGED FILE NO. AND TITLE BLOCK SM 05.04.01												
A CONVERTED TO ACAD PB 05.19.95												
REV DESCRIPTION ENGR DATE												
											PRINT TYPE CA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[SCBS-10-01](#) [SCBS-12-01](#) [SCBS-14-01](#) [SCBS-16-01](#) [SCBS-18-01](#) [SCBS-22.5-01](#) [SCBS-4-01](#) [SCBS-6-01](#) [SCBS-8-01](#)