



GROMMET NO.	GROMMET DASH NO.	"W"±.012 [0.3]	"H"±.008 [0.2]	"L" REF	"T" MAX	"T1" MAX	"DR" REMOVABLE PANEL HOLE DIA. RANGE	"DF" FIXED PANEL HOLE DIA. RANGE	MATING PLUNGER	ALTERNATE MATING PLUNGER NO.	PLUNGER DASH NO.
SLG	SL	.425 [10.8]	.079 [2]	.339 [8.6]	.043 [1.1]	.059-.145 [1.5-3.7]	.295-.303 [7.5-7.7]	.315-.323 [8-8.2]	SLPL	SLPB	1L
	1L			.354 [9]	.063 [1.6]	.079-.165 [2-4.2]					2L
	2L			.394 [10]	.098 [2.5]	.118-.205 [3-5.2]					3L
	3L			.461 [11.7]	.161 [4.1]	.181-.272 [4.6-6.9]					4L
	4L			.508 [12.9]	.209 [5.3]	.228-.315 [5.8-8]					1M
	1M	.335 [8.5]	.071 [1.8]	.315 [8]	.043 [1.1]	.059-.146 [1.5-3.7]	.234-.240 [5.95-6.1]	.250-.256 [6.35-6.5]	SLPB	----	2M
	2M			.335 [8.5]	.063 [1.6]	.079-.165 [2-4.2]					3M
	3M			.374 [9.5]	.098 [2.5]	.118-.272 [3-5.2]					4M
	4M			.433 [11]	.161 [4.1]	.181-.272 [4.6-6.9]					1S
	1S			.299 [7.6]	.039 [1]	.079-.158 [2-4]					2S
	2S	.256 [6.5]	.047 [1.2]	.319 [8.1]	.059 [1.5]	.098-.177 [2.5-4.5]	.177-.181 [4.5-4.6]	.185-.189 [4.7-4.8]			



PLUNGER STYLES



NOTES:
1. PLUNGER MATERIAL: NYLON 6, (RMS-120).
2. GROMMET MATERIAL: POLYCARBONATE, (RMS-72).
3. COLOR: BLACK OR WHITE; ADD SUFFIX "-B" OR "-W" TO PART NO.

K	SEE CO 200302 FOR CHANGES	SK	01/06/09
J	SEE CO 200187 FOR CHANGES	S.K.	05/21/08
I	SEE ECN #1157 FOR CHANGES	SJ	4/25/06
H	SEE ECN #944 FOR CHANGES	SK	02/22/05
-	SEE ENG. FOR REVISIONS A-G	-	---
REV.	DESCRIPTION	ENGR.	DATE

TITLE: SNAP LATCH					DWG IN IN [MM]	
CREATED USING SOLIDWORKS	FILE #: SL	DWN: SK	APP: SK	FINAL		
TOLERANCES UNLESS NOTED .XX=±.01 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1	SHEET SIZE: B	DT: 02/22/05	CHKD: RDG	PART #	PRINT TYPE
	RE: RICHCO, INC.	RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060			SEE TABLE	CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[SLG-1L-B](#) [SLG-1L-W](#) [SLG-1M-B](#) [SLG-1M-W](#) [SLG-1S-B](#) [SLG-1S-W](#) [SLG-2L-B](#) [SLG-2L-W](#) [SLG-2M-B](#) [SLG-2M-W](#)
[SLG-2S-B](#) [SLG-2S-W](#) [SLG-3M-B](#) [SLG-3M-W](#) [SLPB-1L-B](#) [SLPB-1L-W](#) [SLPB-1M-B](#) [SLPB-1M-W](#) [SLPB-1S-B](#)
[SLPB-1S-W](#) [SLPB-2L-B](#) [SLPB-2L-W](#) [SLPB-2M-B](#) [SLPB-2M-W](#) [SLPB-2S-B](#) [SLPB-2S-W](#) [SLPB-3M-B](#) [SLPB-3M-W](#)
[SLPL-1L-B](#) [SLPL-1L-W](#) [SLPL-2L-B](#) [SLPL-2L-W](#)