

PART NO.	"A" DIA.	"B" ± 0.015 (± 0.4)	"C" REF.	FIG. NO.
SRC-4-01	1/4 (6.4)	.26 (6.6)	.75 (19.1)	2
SRC-7-01	7/16 (11.1)	.39 (9.8)	.97 (24.7)	1
SRC-8-01	1/2 (12.7)	.43 (10.8)	1.04 (26.5)	
SRC-10-01	5/8 (15.9)	.50 (12.7)	1.18 (29.9)	

FIG. 1







FIG. 2



NOTES:

- MAT'L: NYLON 66 (RMS-01).
FLAME RETARDANT NYLON (RMS-19),
AVAILABLE BY SPECIAL ORDER ONLY.
- COLOR: NATURAL
COLOR BLACK, AVAILABLE BY SPECIAL ORDER

TITLE: SPLIT ROUTING CLIP						DWG IN IN (MM)	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # SRC		DWN: P.B.	APP:	FINAL		
	MAT'L: SEE NOTES		DT: 05-02-95	DT:	PART #		PRINT TYPE
	RE: RICHCO, INC.		RICHCO INC. PO BOX 804238,CHICAGO,60680 (773) 539-4060		SEE TABLE		CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[SRC-10-01](#) [SRC-4-01](#) [SRC-7-01](#) [SRC-8-01](#)