





PART NO.			"A"±.015 (0.4)
FOR #4 (M-3) SCREW	FOR #6 (M-3.5) SCREW	FOR #8 (M-4) SCREW	
SSRS4-2-01	—	—	1/8 (3.2)
SSRS4-3-01	—	—	3/16 (4.8)
SSRS4-4-01	SSRS6-4-01	SSRS8-4-01	1/4 (6.4)
SSRS4-5-01	SSRS6-5-01	SSRS8-5-01	5/16 (7.9)
SSRS4-6-01	SSRS6-6-01	SSRS8-6-01	3/8 (9.5)
SSRS4-7-01	SSRS6-7-01	SSRS8-7-01	7/16 (11.1)
SSRS4-8-01	SSRS6-8-01	SSRS8-8-01	1/2 (12.7)
SSRS4-10-01	SSRS6-10-01	SSRS8-10-01	5/8 (15.9)
—	SSRS6-12-01	SSRS8-12-01	3/4 (19.1)
—	SSRS6-14-01	SSRS8-14-01	7/8 (22.2)
—	SSRS6-16-01	SSRS8-16-01	1.0 (25.4)


SERIES NO.	DIM. "B"	DIM. "C"	SCREW SIZE	MOUNTING HOLE DIA. ±.003(0.08)
SSRS4	.260 (6.6)	.125 (3.1)	#4	.187 (4.75)
SSRS6	5/16 (7.9)	.153 (3.9)	#6	.234 (5.94)
SSRS8	5/16 (7.9)	.169 (4.3)	#8	.234 (5.94)

TO LOCK IN A .062 (1.57)
THICK PANEL

NOTES:

1. MATERIAL: NYLON 66 (RMS-01).
FLAME RETARDANT: NYLON (RMS-19),
BY SPECIAL ORDER.
2. COLOR: NATURAL.

TITLE: STACKABLE, SELF RETAINING SPACER



DWG IN
IN (MM)



FINAL

PART #
SEE TABLE

PRINT
TYPE
CA

D	CHANGED FILE NUMBER	SM 05.10.01
C	ADDED 3 NEW SIZES TO #6 & #8 SCREW	M.B. 9.15.00
B	DIM. 5/16(7.9) WAS 5/16(7.1)	J.L. 4/22/99
A	MAT'L RMS-19 ADDED	J.L. 12.10.97
REV	DESCRIPTION	ENGR DATE

TOLERANCES
UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=1/64
ANG=1°

FILE # SSRS
MAT'L: SEE NOTES
RE: RICHCO, INC.

DWN: P.B.
DT: 03-16-94
APP:
DT:
RICHCO INC.
PO BOX 804238, CHICAGO, 60680
(773) 539-4060

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[SSRS6-12-01](#) [SSRS4-8-01](#) [SSRS4-2-01](#) [SSRS6-6-01](#) [SSRS6-8-01](#) [SSRS4-10-01](#) [SSRS4-3-01](#) [SSRS4-4-01](#)
[SSRS4-5-01](#) [SSRS4-6-01](#) [SSRS4-7-01](#) [SSRS6-10-01](#) [SSRS6-14-01](#) [SSRS6-16-01](#) [SSRS6-4-01](#) [SSRS6-5-01](#)
[SSRS6-7-01](#) [SSRS8-10-01](#) [SSRS8-12-01](#) [SSRS8-14-01](#) [SSRS8-16-01](#) [SSRS8-4-01](#) [SSRS8-5-01](#) [SSRS8-6-01](#)
[SSRS8-7-01](#) [SSRS8-8-01](#)