




PART NO.	THREAD TYPE
TB-1	#6-32
TB-2	#8-32
TB-3	M3
TB-4	M4



NOTES:

1. MATERIAL: RUBBER BUMPER - IIR, SHORE 40-50A DUROMETER (RMS-348)
THREADED STEM - BRASS (RMS-349)
2. COLOR: RUBBER BUMPER - BLACK
THREADED STEM - AS MACHINED
3. TYPICAL COMPRESSION FOR 10 LB MAX LOAD = .03 [0.8]

				TITLE: THREADED BUMPERS						DWG IN IN[MM]	
				CREATED USING SOLIDWORKS	FILE #: TB		DWN: S.J.	APP: S.J.		FINAL	
				TOLERANCES UNLESS NOTED	SHEET: 1 OF 1		SHEET SIZE: A		DT: 1.09.07	CHKD: S.K.	
				.XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	RE: RICHCO, INC.		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		PART # SEE TABLE		PRINT TYPE CA
B	SEE ECN #1309 FOR CHANGES			SK	04/05/07						
A	RELEASED FOR PRODUCTION			SK	01/09/07						
REV.	DESCRIPTION			ENGR.	DATE						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[TB-3](#) [TB-1](#) [TB-2](#) [TB-4](#)