



NYLON 6/6 (RMS-01) COLOR: NATURAL PART NO.	FLAME RET. (RMS-19) COLOR: NATURAL PART NO.	DIM "A" ±.015 (±0.4)	DIM "B" ±.015 (±0.4)
TCBS-4-01	TCBS-4-19	1/4 (6.4)	13/64 (5.2)
TCBS-6-01	TCBS-6-19	3/8 (9.5)	5/16 (7.9)
TCBS-8-01	TCBS-8-19	1/2 (12.7)	
TCBS-10-01	TCBS-10-19	5/8 (15.9)	
TCBS-12-01	TCBS-12-19	3/4 (19.1)	
TCBS-14-01	TCBS-14-19	7/8 (22.2)	
TCBS-16-01	TCBS-16-19	1 (25.4)	
TCBS-18-01	TCBS-18-19	1-1/8 (28.6)	
TCBS-20-01	TCBS-20-19	1-1/4 (31.7)	
TCBS-22.5-01	TCBS-22.5-19	1-13/32 (35.7)	

TITLE: SCREW-MOUNT CIRCUIT BOARD SUPPORT				DWG IN IN (MM)	FINAL
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # TCBS	DWN: P.B.	APP:	PART # SEE TABLE	
	MAT'L: SEE NOTES	DT: 01-23-95	DT:		
	RE: RICHCO INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		PRINT TYPE CA	

B	REMOVED NOTES. AND CHANGED FILE NO.	SM 04.19.02
A	CONVERTED TO ACAD	PB 01.23.95
REV	DESCRIPTION	ENGR DATE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Essentra:

[TCBS-10-01](#) [TCBS-10-19](#) [TCBS-12-01](#) [TCBS-12-19](#) [TCBS-14-01](#) [TCBS-14-19](#) [TCBS-16-01](#) [TCBS-16-19](#) [TCBS-4-01](#) [TCBS-4-19](#) [TCBS-6-01](#) [TCBS-6-19](#) [TCBS-8-01](#) [TCBS-8-19](#) [TCBS-18-01](#) [TCBS-18-19](#) [TCBS-20-01](#) [TCBS-20-19](#) [TCBS-22.5-01](#) [TCBS-22.5-19](#)