


PART NO.	"A"	"B"
TRCG-2.500	2-1/2 (63.5)	2.2 (55.9)
TRCG-3.300	3.3 (83.8)	3 (76.2)
TRCG-3.925	3.93 (99.7)	3-5/8 (92.1)
TRCG-6.675	6.68 (169.6)	6-3/8 (161.9)



NOTES:

- MAT'L: POLYCARBONATE (RMS-23)
COLOR: BLACK

TITLE: TENSION RACK CARD GUIDE					DWG IN IN (MM)			
D	CHANGED MAX BOARD THICKNESS TO 2.2MM	SJ 02.06.02	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.010 FRAC=1/64 ANG=1°	FILE # TRCG	DWN: P.B.	APP:	FINAL	
C	CHANGED FILE NUMBER	SM 05.11.01	RE: RICHCO, INC.	MAT'L: SEE NOTES	DT: 09-14-94	DT:	PART #	
B	DIM'S PUT TO 3 PLACES; DIM. .093 REMOVED	PB 08.18.95		RICHCO INC. PO BOX 804238,CHICAGO,60680 (773) 539-4060		SEE TABLE		PRINT TYPE CA
A	RECOMMENDED MOUNTING HOLES ADDED; DIM. .128 DIA. HOLE WAS .123 DIA. HOLE; NOTE 1 ADDED	PB 06.09.95						
REV	DESCRIPTION	ENGR DATE						

TOLERANCES
UNLESS NOTED
.XX= $\pm .010$
.XXX= $\pm .010$
FRAC=1/64
ANG=1°

FILE # TRCG

DWN: P.B.

APP:

MAT'L: SEE NOTES

DT: 09-14-94

DT:

RE: RICHCO, INC.

RICHCO INC.
PO BOX 804238, CHICAGO, 60680
(773) 539-4060

PART #

SEE TABLE

CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[TRCG-2.500](#) [TRCG-3.300](#) [TRCG-3.925](#) [TRCG-6.675](#)