



Ø.125 [3.2] / Ø.128 [3.3]




48.00 ±.50
[1219.2 ±12.7]

SECTION A-A
SCALE 2.5 : 1


.125 [3.2] / .128 [3.3] .22 [5.5]



48.34 ±.50
[1227.8 ±12.7]
MOUNTING HOLES




.36 [9.1]



.32 [8.1]

.17 [4.3] .25 [6.4]

ACCEPTS 1/16 [1.6]
THICK BOARD




.22 [5.6]

.15 [3.7]


P/N: ACGE-01

1. MATERIAL: NYLON 6/6 (RMS-01)
2. COLOR: NATURAL



ADJUSTABLE CARD GUIDE CHANNEL
P/N: ACGC-4800

ADJUSTABLE CARD GUIDE END
P/N: ACGE-01



.31 [7.9]

.34 [8.7]

P/N: ACGC-4800

1. MATERIAL: PVC (RMS-04)
2. COLOR: NATURAL

NOTES:
1. PART NO. ACGC-4800 CAN BE CUT TO ANY LENGTH BY SPECIAL ORDER.
EXAMPLE: IF MOUNTING HOLES DISTANCE IS 5.00 [127.0], SUBTRACT .34 [8.6] FROM IT.
THEN YOUR CHANNEL LENGTH IS 4.66 [118.4].

E	SEE CO 200462 FOR CHANGES	SK	10/23/05
D	SEE ECN #1018 FOR CHANGES	SK	06/14/05
C	SEE ECN #800 FOR CHANGES	SM	06/14/04
B	P/N WAS ACGC-04 AND FILE # WAS 03060	SM	11.15.00
A	CONVERTED TO ACAD	PB	01.16.95
REV.	DESCRIPTION	ENGR.	DATE

TITLE: ADJUSTABLE CARD GUIDE							
CREATED USING SOLIDWORKS	FILE #: ACGC-ACGE		DWN: P.B.	APP: -	FINAL		
TOLERANCES UNLESS NOTED XX=±.010 XXX=±.005 FRAC =±1/64 ANG =±1°	SHEET: 1 OF 1	SHEET SIZE: B	DT: 01/16/95	CHKD: -	PART #	PRINT TYPE	
	RE: RICHCO, INC.		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		SEE DRAWING	CA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[ACGC-4800](#) [ACGE-01](#)